

PREP M

'WASH PREP' / CLEANER AND ADHESION PROMOTER

8 December 2017

YOUR SMART ADVANTAGES

- Fast drying approximately 5 minutes
- Easy to use as 'wash Prep'
- Efficient in use

USFS

- Pre-treatment of ceramic coated glass
- Pre-treatment of lacquered/painted metals.
- Pre-treatment of polyester (GRP)
- Pre-treatment of powder coated metals.
- Pre-treatment of plain aluminum, steel, copper and brass surfaces.

APPLICATION INSTRUCTIONS

- Ensure that substrates (e.g. freshly painted metalflange, windscreen) are clean, dust and grease free
- 2) Remove inner protective metal seal of can.
- 3) **IMPORTANT NOTE:** Don't use Simson 'Wash Prep" M that has a milky appearance.
- 4) Ensure that Simson Prep M is applied very thinly
- 5) Firmly rub the bond-areas with a clean, lint and colour free cotton cloth or tissue, wetted with Simson prep M.
- 6) Allow to dry for approximately 5 minutes before applying Simson Adhesive/Sealant on ceramic coated glass with adequate U.V. Blackout or the freshly painted metal-flange.
- If the glass does not have a black ceramic band, apply Simson Prep G Extra. Do not use Simson Prep M as 'Prep" cleaner but use Bostik N40 Primer.

For instructions refer to Data Sheet Simson Prep G Extra and Bostik N40 Primer. Also refer to Technical Data Sheet Simson ISR 70 – 08AP.

PRECAUTION

Simson Prep M should not be applied on those areas which have to be painted afterwards, due to paint incompatibility of Simson Prep M. In this case only apply.

Simson Prep M on that area where the sealant or adhesive will be applied by use of e.g. masking tape (however it is possible to remove residues of Simson Prep M afterwards from the cleaned surfaces by use of Isopropyl alcohol (IPA)).

PRODUCT CHARACTERISTICS	
Solids Content	Approx. 17%
Specific Gravity	Approx. 0.76
Flash Point	+9°C
Drying Time	Approx. 5 minutes
Colour	Transparent
Coverage	Approx. 20m²/L
Product code 250ml - Clear 1 Litre - Clear	30608604 30608483

STORAGE & SHELF LIFE

Store in a cool, dry place, out of direct sunlight and away from all sources of ignition. Storage areas must be well ventilated and comply with Local, State and Federal regulations. For maximum shelf life, store between 5°C and 20°C.

Simson Prep M has a 1 year shelf life when stored in original, unopened containers, under the above conditions.

Simson Prep M will have up to 90 days shelf life after breaking the inner protective metal seal. Protect contents from contamination and evaporation. Ensure can is tightly sealed with plastic cap after use and store in a well ventilated area.

FLAMMABILITY

Simson Prep M is highly flammable.

Version 11 Page 1 of 2

PREP M 'WASH PREP' / CLEANER AND ADHESION PROMOTER

For emergency information contact the Poisons Information Centre, phone 131 126 or the Emergency Response Service, phone 1800 033 111.



This datasheet is for the general help of users. It is provided in good faith. The data is current and accurate to the best of our knowledge. Differing materials, substrates, environments, site conditions, and product storage, handling and application may affect results. Users should carry out tests to decide the product's suitability for purpose. This data sheet and the properties of the product may change without notice. Users, suppliers and retailers should check that the data sheets they have are the latest. To the maximum extent permitted by law, Bostik disclaims all warranties in relation to manufacture and use of the product. Bostik is not liable for representations made by users, suppliers or retailers about the product. Bostik is not liable for any loss or damage resulting from incorrect, careless, or negligent use or storage of the product, including use of out of date product. Any liability arising from use of the product is limited to the replacement or purchase price of the product. Bostik does not exclude rights and remedies that cannot be excluded by legislation, for example under the Australian Consumer Law (ACL). Sale of the product by Bostik is subject to the Bostik Australia Proprietary Limited Conditions and Terms of Sale. For more information on Bostik, products, and conditions of use and sale visit www.bostik.com/au

Bostik Australia Pty Ltd, Level 1, 6 English St, Essendon Fields, Vic, 3041, Australia. Tel: +61 3 9279 9333 www.bostik.com.au

Version 11 Page 2 of 2